

Isomap

www.isomap.ch



STRIPPING

of enamelled wire – with Swiss precision



ISOMAP AG
Obere Bahnhofstrasse 4
CH-3700 Spiez, Switzerland
info@isomap.ch

Isomap



Isomap IIB Handheld Device

STRIPPING

of enamelled wire with Swiss precision




Isomap AG
www.isomap.ch
info@isomap.ch




ISOMAP IIB

The Isomap IIB Handheld Device features a sturdy design and allows quick, clean and precise stripping of all standard enamelled wires with a diameter of 0.2 mm to approx. 7.0 mm, and stranded wires up to 4.5 mm in diameter.



HOW TO USE



Insert the enamelled wire into the protective cap and start rotation

Remove the enamelled wire from the protective cap



SPECIAL FEATURES

- High-quality product
- Speed settings on the device
- Easy controls
- Centring of the wire through the opening in the protective cap
- Suitable for a large range of wire diameters
- Strips up to 55 mm off the wire
- Footswitch mode
- Extensive range of accessories

SCOPE OF DELIVERY



1. Isomap IIB Handheld Device
2. Stripper head
3. Protective cap
4. Pin wrench
5. Regulating pin

Insertable stripper heads

For enamelled wire:

- KG0** Ø 0.2 - 1.2 mm
- KG1** Ø 0.75 - 1.5 mm
- KG2** Ø 1.5 - 3.0 mm
- KG3** Ø 2.2 - 4.5 mm
- KG4** Ø 4.0 - 7.0 mm


For stranded wire

- CR1** up to Ø 2.5 mm
- CR2** Ø 2 - 4.5 mm

For coaxial wire

- GF** up to Ø 6 mm

ACCESSORIES



SPECIFICATIONS

Scope of application	Enamelled wire, stranded wire, coaxial wire
Standard range for enamelled wire	Diameter 0.2 mm to 7 mm
Speed	Infinite settings
Mains voltage	230 V / 50 Hz; 120 V / 60 Hz
Weight	1.31 - 1.47 kg (depending on configuration)