

Isomap

www.isomap.ch



STRIPPING

of enamelled wire with Swiss precision



ISOMAP AG
Obere Bahnhofstrasse 4
CH-3700 Spiez, Switzerland
info@isomap.ch

Isomap



Isomap ACCU S Mini Handheld Device

STRIPPING

of enamelled wire with Swiss precision




Isomap AG
www.isomap.ch
info@isomap.ch




ISOMAP ACCU S

Introducing the latest-generation Isomap ACCU S Mini Handheld Device – a handy, lightweight and cordless device that can be charged with USB. This device cleanly and easily removes the insulation from enamelled wires between 0.2 mm and 1.6 mm in diameter. It can also be used to strip stranded wire.



HOW TO USE



SPECIAL FEATURES

- Cordless
- Ergonomic design
- Speed settings on the device
- Easy controls
- Centring of the wire through the opening in the protective cap
- Low body weight
- Strips up to 55 mm off the wire
- Can be used while charging



Scope of delivery

1. Isomap ACCU S Mini Handheld Device
2. Stripper head
3. Protective cap
4. Pin wrench
5. Regulating pin
6. USB charging cable
7. USB charger
8. Stop pin

Insertable stripper heads

For enamelled wire

KG0 Ø 0.2 - 1.6 mm

For stranded wire

CR1 up to Ø 2.5 mm

SPECIFICATIONS



Rechargeable battery
3.6 V, 7.2 Wh
(built-in rechargeable battery)



Speed
Infinite settings



Application
Enamelled wire, stranded wire

Scope of application	Enamelled wire, stranded wire
Standard range for enamelled wire	Diameter 0.2 mm to 1.6 mm
Standard range for stranded wire	Max. diameter 2.5 mm
Speed	Infinite settings
Input	3.6 V, 7.2 Wh
Rechargeable battery	Built-in
Charging time	2.75 h
Weight	340 g
Dimensions	Length: 23.5 cm Width: 4.0 cm Depth: 4.3 cm
Sound pressure	- 70 dB(A)
Accessories	Length stop, USB power adapter, stripper heads, spare blades